



BA Optima Endodontic Unit



B.



C.



D.

BAE300/350

Compact and ergonomic, simple to use table top endodontic motor.

KEY FACTS

- Auto reverse function • Useable on battery for up to 5 hours or with supplied adaptor
- Reducing gear ratio up to 16:1 • Torque control from 0.6 to 5.2N.cm • 9 programs
- Foot control and handpiece stand included • Dimensions H139 x W110 x D196mm

BA Optima E+ BAE300

Model	Description
A. BAE300	Complete unit with A-type motor (BAE05)
C. BAE05	Endo head for A-type motor

BA Optima E+ BAE350

Code	Description
B. BAE350	Complete unit with E-type motor (BAE15)
D. BAE15	Endo contra-angle head for E-type motor

BA NiTi

Endo Contra-Angle



1. BAE45



2. BA Clips

BAE35/45

KEY FACTS

- Endodontic contra-angle with torque control, direct connection to the motor (no tabletop unit required) • 2 models available: BAE35 115:1 reducing handpiece for electric micromotors, and BAE45 66:1 for air motors • Can be used with all the common NiTi files • Easy torque setting with the unique magnetic ring (5 torque levels) • Retro-rotation system prevents any excessive torque • Optional apex clip connection

1. BA NITI

Code	Description
A. BAE35	115:1 Endo contra-angle
B. BAE45	66:1 Endo contra-angle

2. BA Clip

Code	Description
BAE35C1	2mm Clip for BA NiTi endo c/a
BAE35C2	1.5mm Clip for BA NiTi endo c/a

BA Optima

Endodontic Contra-angle & Head



1. BAE05

2. BAE15

BAE05/BAE15

Endodontic contra-angle and head.

KEY FACTS

- BAE05 - Endo head for A-type motor, compatible with BAE300 unit and BAE370R unit • BAE15 - Endo contra-angle for E-type motor, compatible with BAE350 unit • Gear ratio: 16:1

BA Optima BAE05/BAE15

Code	Description
1. BAE05	Endo head for A-type motor
2. BAE15	Endo contra-angle for E-type motor